

CAT. N° 8 320 32



FUSED CONNECT UNIT SYNERGY -UNSWITCHED + CORD -13 A-250 V~ SLEEK DESIGN BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	169,00

Product characteristics

Fused connection units unswitched 13 A - 250 V~

- Conform to BS 1363: Part. 4
- Front cable outlet with cord grip
- Fuses supplied
- Locked captive fuse carrier (padlockable)
- For flush-mounting, back box to be min. 35 mm deep
- Supplied with 1 gang side extension (3 mm thick) in case of extra wiring space needed
- Nominal plate dimensions: 86 x 86 mm

Unswitched - with cord outlet

- Brushed stainless steel

General characteristics

Synergy™ - cooker control units, fused connection units and cable outlets - SLEEK DESIGN

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.593\)](#)

Agreements & certificates of conformity

- [ASTA-880](#)

Installation & technical data

- [F02656EN-00](#)