

CAT. N° 8 320 60

**BRITISH STANDARD SYNERGY -DOUBLE POLE 1 GANG SWITCH -13 A -250 V~ SLEEK DESIGN BRUSHED STAINLESS STEEL**

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	165,00

Product characteristics**Double pole socket outlets 13 A - 250 V~**

- Conform to BS EN 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm (1 gang), 86 x 146 mm (2 gang)
- ASTA licence

1 gang switched

- Brushed stainless steel

General characteristics**Synergy™ - British standard socket outlets and USB sockets - Sleek Design**

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation **Catalogue pages & additional information**

- [Description page \(p.592\)](#)

 **Agreements & certificates of conformity**

- [ASTA - 780](#)

 **Installation & technical data**

- [F02264EN-00](#)