

CAT. N° 8 322 29



COOKER CONTROL UNIT SYNERGY -250 V~ 45 A+13 A DOUBLE POLE SWITCH+LED SLEEK DESIGN POLISHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,769
Weight (g)	342,00

Product characteristics

Cooker control units - 250 V~

- Conform to BS 4177: 1992
- For flush-mounting, back box to be min. 47 mm deep
- Nominal plate dimensions: 86 x 146 mm

45 A DP switch + 13 A DP switched socket outlet - with blue LED power indicator

- Polished stainless steel

General characteristics

Synergy™ - cooker control units, fused connection units and cable outlets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.593\)](#)

Agreements & certificates of conformity

- [OC / CB - FR_707920](#)

Installation & technical data

- [F02365EN-00](#)