

CAT. N° 8 322 79



SINGLE POLE BRITISH STANDARD SOCKET + USB CHARGER SYNERGY -2 GANG SWITCHED 13 A -SLEEK DESIGN POLISHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,77
Weight (g)	292,00

Product characteristics

Single pole socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2
- USB charger conform to IEC 60950-1

2 gang switched

- USB Type-A + Type-C™ 3 A - 5 VDC - 15 W
- Consumption in passive mode less than 0.08 W
- Polished stainless steel

General characteristics

Synergy™ - British standard socket outlets and USB sockets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.592\)](#)

Agreements & certificates of conformity

- [OC / CB - SE-88178M1](#)

Installation & technical data

- [F02762EN-00](#)