

CAT. N° 8 324 76

**BRITISH STANDARD SYNERGY -SINGLE POLE 2 GANG SWITCH -13 A -250 V~ SLEEK DESIGN GLOSSY GOLD**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,769
Weight (g)	261,00

**Product characteristics****Single pole socket outlets 13 A - 250 V~**

- Conform to BS EN 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep

**2 gang switched**

- Nominal plate dimensions: 86 x 146 mm
- Glossy gold

**General characteristics****Synergy™ - British standard socket outlets and USB sockets - Sleek Design**

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.591\)](#)

 **Agreements & certificates of conformity**

- ASTA - 780

 **Installation & technical data**

- [F02263EN-00](#)