

CAT. N° 8 324 79



## SINGLE POLE BRITISH STANDARD SOCKET + USB CHARGER SYNERGY - 2 GANG SWITCHED - 13 A 250 V~ - SLEEK DESIGN GLOSSY GOLD

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,77
Weight (g)	290,00

### Product characteristics

#### Single pole socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2
- USB charger conform to IEC 60950-1

#### 2 gang switched

- USB Type-A + Type-C™ 3 A - 5 VDC - 15 W
- Consumption in passive mode less than 0.08 W
- Glossy gold

### General characteristics

#### Synergy™ - British standard socket outlets and USB sockets - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.592\)](#)

#### Agreements & certificates of conformity

- [OC / CB - SE-88178M1](#)

#### Installation & technical data

- [F02762EN-00](#)