

CAT. N° 8 330 04



PLATE SWITCH SYNERGY -4 GANG -2 WAY -10 AX -250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,769
Weight (g)	211,00

Product characteristics

Single pole plate switches 10 AX - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep

4 gang - 2-way switches

- Nominal plate dimensions: 86 x 146 mm
- Brushed stainless steel

General characteristics

Synergy™ - single pole switches and dimmers - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.585\)](#)



Agreements & certificates of conformity

- [ASTA - 781](#)
- [QC / CB - FR_708093](#)



Installation & technical data

- [F02249EN-01](#)