

CAT. N° 8 330 12



DOUBLE POLE SWITCH SYNERGY -BLUE LED POWER INDIC. -20 A -250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	135,00

Product characteristics

Double pole switches 20 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 25 mm deep
- Use cord outlet accessory Cat.No 7 300 53 for external cord outlet
- Nominal plate dimensions: 86 x 86 mm

DP switches + blue LED power indicator

- Brushed stainless steel

General characteristics

Synergy™ - fan switch and double pole switches - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.586\)](#)

Agreements & certificates of conformity

- [ASTA - 782](#)
- [OC / CB - FR_708093](#)

Installation & technical data

- [F02252EN-01](#)