

CAT. N° 8 330 29



COOKER CONTROL UNIT SYNERGY -45 A + 13 A DOUBLE POLE SWITCHED -LED -AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,769
Weight (g)	317,00

Product characteristics

Cooker control units - 250 V~

- Conform to BS 4177: 1992
- For flush-mounting, back box to be min. 47 mm deep
- Nominal plate dimensions: 86 x 146 mm

45 A DP switch + 13 A DP switched socket outlet with blue LED power indicator

- Brushed stainless steel

General characteristics

Synergy™ - cooker control units and fused connection units - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.589\)](#)

Agreements & certificates of conformity

- [OC / CB-FR_707920](#)
- [G-MARK-LVE-2020-000985](#)

Installation & technical data

- [F02658EN-00](#)