

CAT. N° 8 330 37



FUSED CONNECT UNIT SYNERGY -DOUBLE POLE SWITCH + CORD OUTLET +LED -AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	147,00

Product characteristics

Fused connection units 13 A - 250 V~

- Conform to BS 1363: Part. 4
- Front cable outlet with cord grip
- Fuse supplied
- Locked captive fuse carrier (padlockable)
- For flush-mounting, back box to be min. 25 mm deep

DP switched with blue LED power indicator + cord outlet

- Nominal plate dimensions: 86 x 86 mm
- Brushed stainless steel

General characteristics

Synergy™ - cooker control units and fused connection units - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.589\)](#)

Agreements & certificates of conformity

- [ASTA-880](#)

Installation & technical data

- [F02361EN-00](#)