

CAT. N° 8 330 41

**SAT SOCKET SYNERGY - SINGLE "F" TYPE - AUTHENTIC BRUSHED STAINLESS STEEL**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	139,00

**Product characteristics****Television sockets**

- For flush-mounting, back box to be min. 35 mm deep
- Screened
- Nominal plate dimensions: 86 x 86 mm

**SAT sockets - single "F" type**

- Brushed stainless steel

**General characteristics****Synergy™ - telephone, data sockets and television sockets - Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.586\)](#)