

CAT. N° 8 330 54



TELEPHONE SOCKET SYNERGY -RJ 11/RJ 12 -SINGLE -AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	112,00

Product characteristics

Telephone sockets

- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

RJ 11/RJ 12 - single

- Brushed stainless steel

General characteristics

Synergy™ - telephone, data sockets and television sockets - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.586\)](#)