

CAT. N° 8 330 59

**BRITISH STANDARD SYNERGY -1 GANG UNSWITCHED -2
A 250 V~ -AUTHENTIC BRUSHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics**Socket outlets 2 A - 250 V~**

- Conform to BS 546
- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm

1 gang unswitched

- Brushed stainless steel

General characteristics**Synergy™ - British standard socket outlets -
Authentic**

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation**Catalogue pages & additional information**

- [Description page \(p.588\)](#)

**Installation & technical data**

- [F02267EN-00](#)