

CAT. N° 8 330 61



## DOUBLE POLE BRITISH STANDARD SYNERGY -1 GANG SWITCH+LED -13 A -250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	150,00

### Product characteristics

#### Double pole socket outlets 13 A - 250 V~

- Conform to BS 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep
- ASTA licence

#### 1 gang switched with blue LED power indicator

- Nominal plate dimensions: 86 x 86 mm
- Brushed stainless steel

### General characteristics

#### Synergy™ - British standard socket outlets - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.587\)](#)

#### Agreements & certificates of conformity

- ASTA - 780

#### Installation & technical data

- [F02261EN-00](#)