

CAT. N° 8 330 70



DOUBLE POLE BRITISH STANDARD SYNERGY -2 GANG SWITCHED -13 A -250 V~ - AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm ³)	0,769
Weight (g)	242,00

Product characteristics

Double pole socket outlets 13 A - 250 V~

- Conform to BS 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep
- ASTA licence

2 gang switched

- Nominal plate dimensions: 86 x 146 mm
- Brushed stainless steel

General characteristics

Synergy™ - British standard socket outlets - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.587\)](#)



Agreements & certificates of conformity

- ASTA - 780



Installation & technical data

- [F02261EN-00](#)