

CAT. N° 8 332 01



**PLATE SWITCH SYNERGY -1 GANG -2 WAY -10 AX -250 V~  
- AUTHENTIC POLISHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics**

**Single pole plate switches 10 AX - 250 V~**

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep

**1 gang - 2-way switches**


- Nominal plate dimensions: 86 x 86 mm
- Polished stainless steel

**General characteristics**

**Synergy™ - single pole switches and dimmers - Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation**

 **Catalogue pages & additional information**

- [Description page \(p.585\)](#)

 **Agreements & certificates of conformity**

- [ASTA-781](#)
- [QC / CB-FR\\_708093](#)

 **Installation & technical data**

- [F02249EN-01](#)