

CAT. N° 8 332 57



## RJ 45 CATEGORY 6 SOCKET SYNERGY - TWIN - AUTHENTIC POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Data sockets Cat. 6

- Rapid cable connection
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

#### RJ 45 - twin

- Polished stainless steel

### General characteristics

#### Synergy™ - telephone, data sockets and television sockets - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.586\)](#)