

CAT. N° 8 332 66



SINGLE POLE BRITISH STANDARD SYNERGY -1 GANG SWITCHED -13 A -250 V~ - AUTHENTIC POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Single pole socket outlets 13 A - 250 V~

- Conform to BS 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep
- ASTA licence

1 gang switched

- Nominal plate dimensions: 86 x 86 mm
- Polished stainless steel

General characteristics

Synergy™ - British standard socket outlets - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

Catalogue pages & additional information

- [Description page \(p.587\)](#)

Agreements & certificates of conformity

- [ASTA - 780](#)

Installation & technical data

- [F02260EN-00](#)