

CAT. N° 8 332 99

**BRITISH STANDARD SOCKET OUTLET SYNERGY -2 GANG  
-15 A -127 V~ -AUTHENTIC BRUSHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Socket outlets 15 A - 127 V~**

- For flush-mounting, back box to be min. 35 mm deep

**2 gang**

- Nominal plate dimensions: 86 x 146 mm
- Brushed stainless steel

**General characteristics****Synergy™ - British standard socket outlets - Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.588\)](#)