

CAT. N° 8 333 33



**PLATE SWITCH SYNERGY -3 GANG -2 WAY -20 AX -250 V~
- AUTHENTIC POLISHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Single pole plate switches 20 AX - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 16 mm deep
- Nominal plate dimensions: 86 x 86 mm

3 gang - 2-way switches


- Polished stainless steel

General characteristics

Synergy™ - single pole switches and dimmers - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation

 **Catalogue pages & additional information**

- [Description page \(p.585\)](#)

 **Agreements & certificates of conformity**

- [ASTA-782](#)
- [QC / CB-FR_708093](#)

 **Installation & technical data**

- [F02251EN-01](#)