

CAT. N° 8 333 56

**ROTARY DIMMER SYNERGY - 1 GANG - 2 WAY - 400 W-  
AUTHENTIC POLISHED STAINLESS STEEL**

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

**Product characteristics****Push on/off rotary dimmers 400 W 100-240 V~ - 50/60 Hz**

- Conform to BS EN 60669-1-2
- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm

**1 gang - 2 way**

- Polished stainless steel

**General characteristics****Synergy™ - single pole switches and dimmers -  
Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.585\)](#)

**Agreements & certificates of conformity**

- [OC / CB-SG PSB-IT-00190](#)

**Installation & technical data**

- [F02303EN-00](#)