

CAT. N° 8 334 19



CABLE OUTLET SYNERGY - 20 A 250 V~ - AUTHENTIC GLOSSY GOLD

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	126,00

Product characteristics

Cable outlets

- Conform to BS 5733
- Fitted clamp and outlet membrane
- With terminal block
- Nominal plate dimensions: 86 x 86 mm

20 A - 250 V~

- Glossy gold

General characteristics

Synergy™ - shaver sockets, cable outlets, blanking plates and cord outlets - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.589\)](#)



Installation & technical data

- [F02358EN-00](#)