

CAT. N° 8 334 35



## FUSED CONNECT UNIT SYNERGY -DOUBLE POLE SWITCH WITH BLUE LED -AUTHENTIC GLOSSY GOLD

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Fused connection units 13 A - 250 V~

- Conform to BS 1363: Part. 4
- Front cable outlet with cord grip
- Fuse supplied
- Locked captive fuse carrier (padlockable)
- For flush-mounting, back box to be min. 25 mm deep

#### DP switched with blue LED power indicator

- Nominal plate dimensions: 86 x 86 mm
- Glossy gold

### General characteristics

#### Synergy™ - cooker control units and fused connection units - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.589\)](#)

#### Agreements & certificates of conformity

- [ASTA-880](#)

#### Installation & technical data

- [F02361EN-00](#)