

CAT. N° 8 334 65

**BRITISH STANDARD SYNERGY - 1 GANG UNSWITCHED -  
13 A 250 V~ - AUTHENTIC GLOSSY GOLD**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	125,00

**Product characteristics****Socket outlets 13 A - 250 V~**

- Conform to BS 1363: Part. 2
- With safety shutter mechanism
- For flush-mounting, back box to be min. 25 mm deep
- ASTA licence

**1 gang unswitched**

- Nominal plate dimensions: 86 x 86 mm
- Glossy gold

**General characteristics****Synergy™ - British standard socket outlets -  
Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.587\)](#)

**Agreements & certificates of conformity**

- [ASTA - 780](#)

**Installation & technical data**

- [F02259EN-00](#)