

CAT. N° 8 334 98

**BRITISH STANDARD RCD SYNERGY -ELR DOUBLE POLE
30 MA 2 GANG -13 A -250 V~ -AUTHENTIC GLOSSY GOLD**

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics**RCD sockets 13 A - 250 V~**

- Conform to BS 7288: 1990 and BS 1363 - Part 2: 1995
- Conventional earth pin release shutter
- Maximum operating current 16 A
- Electronic RCD module with a membrane switch for "test and reset"
- Flush mounting back box : min. 25 mm deep

ELR - DP 30 mA - 2 gang

- Trips in the event of a power failure
- Ideal for applications where it is desirable to automatically re-activate equipment after a power failure. E.g. fridge, freezer, unmanned areas
- Nominal plate dimensions: 86 x 146 mm
- Glossy gold

General characteristics**Synergy™ - British standard RCD sockets - Authentic**

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation**Catalogue pages & additional information**

- [Description page \(p.588\)](#)

**Installation instructions & related documents**

- [LE08955AA](#)