

CAT. N° 8 335 56

**ROTARY DIMMER SYNERGY - 1 GANG - 2 WAY - 400 W-
AUTHENTIC GLOSSY GOLD**

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	159,00

Product characteristics**Push on/off rotary dimmers 400 W 100-240 V~ - 50/60 Hz**

- Conform to BS EN 60669-1-2
- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm

1 gang - 2 way

- Glossy gold

General characteristics**Synergy™ - single pole switches and dimmers -
Authentic**

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation**Catalogue pages & additional information**

- [Description page \(p.585\)](#)

**Agreements & certificates of conformity**

- [OC / CB-SG PSB-IT-00190](#)

**Installation & technical data**

- [F02303EN-00](#)