

CAT. N° 500 570



BULKHEAD LIGHT - IP44 - IK04 - ROUND - WITH HF SENSOR - E27 - WITHOUT LAMP

Pack (number of units)	1
Volume (dm ³)	12,065
Weight (g)	1 600,00

Product characteristics

IP 44/54 – IK 04 bulkhead lights to be equipped

Super 400 - IP 44 round bulkhead lights

- With integrated HF sensor - E 27
- Ø296 mm
- Polypropylene base
- Transparent tempered glass diffuser assembled via a 1/4 turn rotation
- Compact fluorescent lamps can be used in bulkhead lights (max. 20 W) with E 27 lamp-holder
- Allows automatic On/Off switching
- Pre-configured settings:
 - time delay: 5 seconds to 25 minutes
 - range: 1 to 8 m
 - light level threshold: 0 to 30 lux
- Consumption: 53 W / 20 W max
- Supplied without lamp

General characteristics

IP 44/54/55 weatherproof bulkhead lights

Documentation



Catalogue pages & additional information

- [Description page \(p.676\)](#)
- [Weatherproof bulkhead lights](#)