

CAT. N° SL189810

LED SHAVERLIGHT - ON/OFF - 800 LM - IP44 - 6.13X50 CM



Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Led shaverlights - IP 44

- Lifetime: 40,000 hours
- Color temperature: 4000 K
- CRI greater than 80
- Opal diffuser for better distribution of the luminous flux
- Screwless connection terminals

800 lm

- Dimensions: 6.13 cm x 50 cm
- ON/OFF

General characteristics

Shaverlights

Documentation



Catalogue pages & additional information

- [Description page \(p.644\)](#)