

CAT. N° ZU51510115

STRAIGHT LENGHT MS100 100A 1+1 OUTLETS - 1.5M



Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Straight elements


- L : 1.5 m
- Outlets : 1+1


General characteristics

MS mini busbars - trunking components

- Reference standard: IEC 61439-6
- Reference temperature: 40 °C
- Degree of Protection: IP 40/55
- Thickness: 0.8 mm
- Dimension: 39x97mm
- N° of conductors: 4 with equal section 3P+N
- Conducting «fire retardant» in accordance with EN 60332-3
- Separation between the conductors by plastic insulators reinforced with 20% glass fiber, which guarantees a degree of V1 self-extinguishing (according to UL94) and conform to the glow-wire test according to IEC 60695-2-10

Documentation

 **Installation instructions & related documents**
■ [LE10249AA](#)

 **Installation & technical data**
■ [LE10249AA](#)