

CAT. N° ZU51520114

## STRAIGHT LENGHT MS160 160A 1+1 OUTLETS - 1M



Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Straight elements

- L : 1 m
- Outlets : 1+1

### General characteristics

#### MS mini busbars - trunking components

- Reference standard: IEC 61439-6
- Reference temperature: 40 °C
- Degree of Protection: IP 40/55
- Thickness: 0.8 mm
- Dimension: 39x97mm
- N° of conductors: 4 with equal section 3P+N
- Conducting «fire retardant» in accordance with EN 60332-3
- Separation between the conductors by plastic insulators reinforced with 20% glass fiber, which guarantees a degree of V1 self-extinguishing (according to UL94) and conform to the glow-wire test according to IEC 60695-2-10

### Documentation

#### Installation instructions & related documents

- [LE10249AA](#)

#### Environmental product profile

- [LGRP-2014-120-V1-EN](#)

#### Installation & technical data

- [LE10249AA](#)