

Product sheet



LEGRAND

Emergency luminaire URA ONE - autotest & addressable M/NM - 3h - 100 lm - LED

REF. 662640 | EAN. 3414970312754

> [Visit e-catalogue](#)

Product characteristics

- URA ONE - indoor self - contained emergency lighting luminaire LED - LED non-maintained and maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs with optimized lighting distribution - Low consumption switching power supply. Fully recyclable - Plug - in back with pre - cutted holes grid to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5mm². IP 42 - IK 07 - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours. Charge monitor with a green LED. Opal diffuser - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51 - Decorative frame to enhance surface - mounting aesthetic integration Cat.Nos 6 616 54/55
- Autotest and addressable luminaires - Maintained/non-maintained (M/NM) - Autotest/addressable luminaires incorporate an automatic self - testing system in order to check the emergency mode - Tests result is visible on 2 signalling LEDs (green - OK and yellow - defective) - Addressable function is activated by setting an ID on each luminaire with infrared configuration tool (Cat.No 0 626 10) and wiring a complementary BUS line - Operating state of all addressable luminaires can be centralized by the control interface (Cat.No 0 626 00) and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building's plan on Legrand Vision System (LVS2) PC software (Cat.No 0 626 02) - These Maintained luminaires can also operate in non-maintained mode according to the wiring of normal lighting - 100 lm - 3h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

-  S000083576FR-3.pdf | PDF (3.97Mo)
-  LE06558AF.pdf | PDF (2.27Mo)
-  S000083576EN_3.pdf | PDF (4.07Mo)

CAD & Design specs / BIM

Legrand_Emergencia_URA_ONE_EXPORT_EN.rfa | RFA (1.74Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0907.pdf | PDF (0.06Mo)
-  ex223001_0906.pdf | PDF (0.09Mo)
-  Legrand 662640 URAONE 100LM-3H M.zip | ZIP

Agreements & Certificates

-  AENOR S-007/000004 | (0.91Mo)
-  LGRP-00661-V01.01-EN.pdf | PDF (0.61Mo)
-  OC / CB-ES1842-M1-AENOR | (0.41Mo)
-  AENOR-007/001689 | (0.9Mo)
-  OC / CB-ES1842 | (0.47Mo)