

Product sheet



LEGRAND

Adaptation plate of the universal backbox for a floor box capacity 8 modules vertical or 12 modules horizontal

REF. 088081 | EAN. 3414970755667

> [Visit e-catalogue](#)

Product characteristics

- Galvanised steel material.
- Possibility of adding reinforcing rods on its sides through 4 pre - drilled ledges (diameter 10mm)
- Installation : reuse the four Fixing screws of the upper plate of the universal backbox.

Recommendation / Restriction

- Indoor use only.

The product's benefits

Installation

- Floor box modular to compose : matchs with your needs (type of installation, number of modules, finishes), gives time for reflexion, protects the product during the progression of the work site (the installation follows the steps of the site).

Usage

- Flush with the concrete screed, the adaptation plate will naturally be covered by the final coating to ensure a perfect integration of the floor box.

Avantages

- Allows a without tool installation of the standard floor box by clipping.

Documentation

TECHNICAL DOCUMENTATION

-  F03334EN-02.pdf | PDF (7.03Mo)
-  F03335EN-03.pdf | PDF (4.72Mo)
-  F03335FR-03.pdf | PDF (4.73Mo)
-  F03334FR-02.pdf | PDF (7.12Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_1143.pdf | PDF (0.46Mo)
-  ex223001_1146.pdf | PDF (0.48Mo)
-  ex223001_1140.pdf | PDF (0.12Mo)
-  ex223001_1153.pdf | PDF (0.4Mo)
-  ex223001_1144.pdf | PDF (0.05Mo)
-  ex223001_1147.pdf | PDF (0.47Mo)
-  ex223001_1145.pdf | PDF (0.12Mo)

CAD & Design specs / BIM

- Legrand_universal_round_floor_boxes_EN.rfa | RFA (1.09Mo)
- Legrand_boites_de_sol_univ_affleurant_FR.rfa | RFA (1.45Mo)
- legrand_boites_de_sol_univ_vers_rde_FR.rfa | RFA (1.09Mo)
- Legrand_universal_std_floor_boxes_NL.rfa | RFA (1.49Mo)
- Legrand_universal_std_floor_boxes_EN.rfa | RFA (1.46Mo)
- Legrand_universal_flush_floor_boxes_NL.rfa | RFA (1.45Mo)
- Legrand_universal_flush_floor_boxes_EN.rfa | RFA (1.45Mo)
- Legrand_universal_round_floor_boxes_NL.rfa | RFA (1.09Mo)
- legrand_boites_de_sol_univ_vers_std_FR.rfa | RFA (1.46Mo)

-  ex223001_1141.pdf | PDF (0.1Mo)
-  ex223001_1142.pdf | PDF (0.51Mo)
-  ex223001_1154.pdf | PDF (0.31Mo)
-  ex223001_1152.pdf | PDF (0.09Mo)

Agreements & Certificates

-  LGRP-00109-V01.01-EN.pdf | PDF (0.61Mo)
-  LGRP-00108-V01.01-EN.pdf | PDF (0.61Mo)