

Product sheet



LEGRAND

KNX fan coil unit controller 1-10v or on/off 2 pts valves
 REF. 049041 | EAN. 3414970795052

> [Visit e-catalogue](#)

Product characteristics

- 5 channel 10A relay outputs
- 2 channel 0 - 10V DC outputs
- 3 Fan speeds : High, Medium, Low
- Operating voltage supplied by the bus: 21...30 V DC
- DIN 4 modules

Recommendation / Restriction

- Configuration through ETS tool from KNX association

The product's benefits

Installation

- Connected with the BUS/KNX cable

Usage

- Can be used to control heating floor through up to 5 switching outputs

Avantages

- Operating mode: Standby, Comfort, Night and Protection according to user's demands
- Control based on two-step control or a time-discrete PI controller

Documentation

TECHNICAL DOCUMENTATION

- [LE09376AA.pdf](#) | PDF (0.23Mo)
- [S000093715EN-2.pdf](#) | PDF (3.35Mo)
- [S000093715FR-2.pdf](#) | PDF (3.72Mo)

Agreements & Certificates

- [KNX EIB-11/13887/17](#) | (0.79Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0894.pdf](#) | PDF (0.05Mo)

Software & configurators

- [FW_LG-049041.zip](#) | ZIP (3.32Mo)
- [Cas_d_usage_049041_2t_0_10V_1.zip](#) | ZIP (2.29Mo)
- [Use_case_049041_4t_0_10V_ON_OFF_1.zip](#) | ZIP (3.32Mo)
- [FW_LG-002638_2.zip](#) | ZIP (8.46Mo)
- [Cas_d_usage_049041_4t_ON_OFF_1.zip](#) | ZIP (2.22Mo)

-  Use_case_049041_2t_0_10V_1.zip | ZIP (2.29Mo)
-  Cas_d_usage_049041_4t_0_10V_1.zip | ZIP (2.22Mo)
-  Cas_d_usage_049041_2t_PWM_1.zip | ZIP (2.28Mo)
-  Use_case_049041_4t_0_10V_1.zip | ZIP (2.22Mo)
-  Use_case_049041_2t_PWM_1.zip | ZIP (3.17Mo)
-  Cas_d_usage_049041_4t_0_10V_ON_OFF_1.zip | ZIP (2.36Mo)
-  Use_case_049041_2t_ON_OFF_1.zip | ZIP (3.15Mo)
-  Use_case_049041_4t_PWM_1.zip | ZIP (3.11Mo)
-  Cas_d_usage_049041_2t_ON_OFF_1.zip | ZIP (2.27Mo)
-  Cas_d_usage_049041_4t_PWM_1.zip | ZIP (2.23Mo)
-  Use_case_049041_4t_ON_OFF_1.zip | ZIP (3.09Mo)