

Product sheet



LCS³ LEGRAND

6 connectors RJ45 Category 6 UTP

REF. 033763 | EAN. 3414970870599

This RJ45 connector is to be installed in flat or angled (1U 24 and 48 slots) patch panels. Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for tool-less installation and maintenance.

> [Visit e-catalogue](#)

Description

This RJ45 connector is to be installed in flat or angled (1U 24 and 48 slots) patch panels. Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for tool-less installation and maintenance.

Product characteristics

- 568 A/B marking
- POE + compliant

Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

The product's benefits

Installation

- User installation is rendered easy through an intuitive fast and secure management of each individual connector.

Usage

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

Avantages

- Connector tested and guaranteed to support POE signals (standard IEEE 802.3af and POE+, draft standards 802.3at) up to 2500 connections and disconnections with load.
- Tests are carried out with 2 simultaneous POE+ circuits producing a minimum total power of 50W.

Documentation

TECHNICAL DOCUMENTATION

S000096849FR-05.pdf | PDF (4.55Mo)

LE09819AB.pdf | PDF (1.07Mo)

S000096849EN-05.pdf | PDF (4.55Mo)

Agreements & Certificates








AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)

AoC-CL2_Cat6UTP3275432861ac1181025 | (0.07Mo)

CATALOGUE PAGE & OTHERS

ex223001_0984.pdf | PDF (0.13Mo)

ex223001_0988.pdf | PDF (0.08Mo)

-  AoC-CL4_Cat6_UTP_32866_ac1181047 | (0.08Mo)
-  AoC-CL4_Cat6_UTP_32754_ac1181046 (| (0.08Mo)
-  AoC-PL2_Cat6_UTP_32754_ac1181024 | (0.07Mo)
-  AoC-PL2_C6_UTP_32886_ac1191056 | (0.06Mo)
-  AoC-PL3_Cat6_UTP_32754_ac1181026 | (0.07Mo)
-  AoC-CL2_C6_UTP_32886_ac1191057 | (0.06Mo)
-  AoC-Composant Cat6 UTP 3P-1200836 | (0.06Mo)