

Product sheet



LEGRAND

Arteor™ - RJ45 socket - category 6A STP - 9 contacts - 1 module - White

REF. 572306 | EAN. 3245065723069

> [Visit e-catalogue](#)

Product characteristics

- Legrand cabling system, LCS³ cat. 6A - RJ 45 sockets - Arteor - Can be integrated in any support - Mechanisms to be equipped with support frames and plates - Equipped with connectors with quick toolless connection - Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables - T568A and B marking with colour codes - Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards
- Cat. 6A RJ 45 sockets - Arteor - Metal shielding STP - 1 module - White

Documentation

TECHNICAL DOCUMENTATION

 F01496EN-04.pdf | PDF (1.38Mo)

→ LE02894AJ.pdf | PDF (2.05Mo)

CAD & Design specs / BIM

 3D_LG-572306.stp | IFC (21.4Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0580.pdf | PDF (0.12Mo)

 ex223001_0981.pdf | PDF (0.11Mo)

Agreements & Certificates

 AoC-PL2_Cat6A_FFTP_32799_ac1171009 | (0.07Mo)

 AoC-CL4_Cat6A_STP_32869_ac1181045 | (0.08Mo)

 AoC-PL2_Cat6A_FTP_32778_ac1171014 | (0.08Mo)

 AoC-4PPoE 2019-676 Ac Delta Force | (0.08Mo)

 AoC-PL2_Cat6A_STP_32777_ac1171017A | (0.08Mo)

 AoC-CL2_Cat6A_STP_32777_ac1171018A | (0.08Mo)

 AoC-CL2_C6A_UFTP_32884_ac1191059 | (0.06Mo)

 AoC-CL2_C6A_STP_32882_ac1191063 | (0.06Mo)

 AoC-CL2_Cat6A_FFTP_32799_ac1171010 | (0.07Mo)

 LGRP-01786-V01.01-EN.pdf | PDF (0.89Mo)

 AoC-CL4_Cat6A_STP_32778_ac1181044 | (0.08Mo)

 AoC-CL2_C6A_FFTP_32883_ac1191061 | (0.06Mo)

 AoC-CL2_Cat6A_FTP_32778_ac1171015 | (0.08Mo)

-  AoC-PL3_Cat6A_FTP_32778_ac1171016 | (0.08Mo)
-  AoC-PL2_C6A_FFTP_32883_ac1191060 | (0.06Mo)
-  AoC-PL3_Cat6A_STP_32777_ac1171019A | (0.08Mo)
-  AoC-PL2_C6A_STP_32882_ac1191062 | (0.06Mo)
-  AoC-PL3_Cat6A_FFTP_32799_ac1171011 | (0.07Mo)
-  LGRP-01786-V01.01-FR.pdf | PDF (0.9Mo)
-  AoC-PL2_C6A_UFTP_32884_ac1191058 | (0.06Mo)