

Product sheet



PRACTIBOX 3 LEGRAND

Practibox 3 flush-mounting DIN cabinet - 2 rows of 12 modules - Smoked door - Earth + Neutral terminal blocks

REF. 401753 | EAN. 3414971257276

> [Visit e-catalogue](#)

Product characteristics

- Delivered with : - Removable chassis equipped with DIN rail ; - Reversible cover and smoked door ; - Removable faceplates (1 per row) ; - Earth + Neutral IP 2X terminal blocks ; - 5M blanking plates .
- Practibox 3 is a guarantee of a high - quality range which complies with the IEC 60670 - 24 and the IEC 62208 standards. This range allows installations compliant with IEC 61439 - 3 standard.
- Practibox 3 plastic cabinet has an IP40 and an IK07 with door, protecting it from impacts and solid bodies larger than 1 mm. Flush-mounting boxes resist to incandescent wire up to 850° to be installed within a masonry or dry wall according to your projects.
- Reversible cabinet and door allowing openings to the left or to the right according to the room configuration. Practibox 3 door opens to 180° and has an easy closing thanks to magnets inside the door.
- Practibox 3 has a wide range of accessories to meet all your needs : - A dedicated kit for joining 2 cabinets horizontally or vertically when installed in masonry (ref. 401723) ; - A dedicated kit to install it in dry partitions (ref. 401724) ; - An horizontal partition (ref. 401722) ; - A plain faceplate (ref. 401725) ; - Perforated plates (ref. 401726) ; - A 12x2 flat bar for IP2X terminal blocks for installing additional ones (ref. 401727) ; - A key lock (ref. 001966).

Recommendation / Restriction

- Indoor flush-mounted installation only.

Documentation

TECHNICAL DOCUMENTATION



F01895FR-06.pdf | PDF (2.13Mo)

The product's benefits

Installation

- From the removable chassis and faceplates through to the rigid and practical flush-mounting box, everything has been designed in Practibox 3 to ensure an easy installation. Moreover, with a large choice of accessories available to facilitate every installation, Practibox 3 gives a premium image on all your high-value projects.

Usage

- These new 'ready-to-use' flush-mounting distribution cabinets are designed to be discreet and elegant with a top quality finish. Fitting close to the wall, the white or smoked finish doors on Practibox 3 cabinets are ultra-flat and smooth in order to blend perfectly with today's interiors.

Avantages

- Practibox 3 has a large offer from 8 modules to 72 modules, designed for all your premium projects in residential or small commercial buildings by covering a wide range of needs. Its attractive appearance with an ultra-flush door and its special ergonomic design give both users and installers maximum ease of use.

CATALOGUE PAGE & OTHERS





ex223001_0316.pdf | PDF (0.31Mo)

 F01895EN-06.pdf | PDF (2.12Mo)

 LE09548AA-01.pdf | PDF (0.61Mo)

CAD & Design specs / BIM

 Legrand_Practibox³_8_and_12_modules_transparent_door.rfa | RFA (1.47Mo)

 Legrand_Practibox³_8_et_12_modules_porte_transparente.rfa | RFA (1.47Mo)

 ex223001_0317.pdf | PDF (0.04Mo)

Agreements & Certificates

 OC / CB-IT-19045 | (0.15Mo)