

CAT. N° 5 723 51



## RJ45 SOCKET ARTEOR - CATEGORY 6A STP - 1 MODULE - WHITE WITH ORANGE SHUTTER

Pack (number of units)	10
Volume (dm <sup>3</sup> )	2,188
Weight (g)	450,00

### Product characteristics

#### Cat. 6A RJ 45 sockets - Arteor

- Metal shielding

#### STP - 1 module

- White with orange shutter

### General characteristics

#### Legrand cabling system, LCS<sup>3</sup> cat. 6A - RJ 45 sockets - Arteor

- Can be integrated in any support
- Mechanisms to be equipped with support frames and plates
- Equipped with connectors with quick toolless connection
- Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
- T568A and B marking with colour codes
- Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.450\)](#)
- [Description page \(p.468\)](#)
- [Description page \(p.733\)](#)



#### Agreements & certificates of conformity

- [AoC-PL2\\_Cat6A\\_FFTP\\_32799\\_ac1171009](#)
- [AoC-CL2\\_Cat6A\\_FFTP\\_32799\\_ac1171010](#)
- [AoC-PL2\\_Cat6A\\_FTP\\_32778\\_ac1171014](#)
- [AoC-CL2\\_Cat6A\\_STP\\_32777\\_ac1171018A](#)
- [AoC-PL3\\_Cat6A\\_FTP\\_32778\\_ac1171016](#)
- [AoC-CL2\\_Cat6A\\_FTP\\_32778\\_ac1171015](#)
- [AoC-PL3\\_Cat6A\\_STP\\_32777\\_ac1171019A](#)
- [AoC-PL2\\_Cat6A\\_STP\\_32777\\_ac1171017A](#)
- [AoC-CL4\\_Cat6A\\_STP\\_32869\\_ac1181045](#)
- [AoC-CL4\\_Cat6A\\_STP\\_32778\\_ac1181044](#)
- [AoC-PL2\\_C6A\\_FFTP\\_32883\\_ac1191060](#)
- [AoC-CL2\\_C6A\\_FFTP\\_32883\\_ac1191061](#)
- [AoC-PL2\\_C6A\\_UFTP\\_32884\\_ac1191058](#)
- [AoC-CL2\\_C6A\\_STP\\_32882\\_ac1191063](#)
- [AoC-4PPoE\\_2019-676\\_Ac\\_Delta\\_Force](#)
- [AoC-CL2\\_C6A\\_UFTP\\_32884\\_ac1191059](#)
- [AoC-PL3\\_Cat6A\\_FFTP\\_32799\\_ac1171011](#)
- [AoC-PL2\\_C6A\\_STP\\_32882\\_ac1191062](#)



#### Installation & technical data

- [F01496EN-04](#)

CAT. N° 5 723 51