

CAT. N° 7 645 82



AUTOMATIC SWITCH NILOÉ - IR - 180° - RANGE 8 M - 3-WIRE WITH NEUTRAL - WHITE

Pack (number of units)	1
Volume (dm ³)	0,534
Weight (g)	98,00

Product characteristics

Automatic switches

- IR detection
- Detection field: 120°
- Detection range: 8 m
- Time delay adjustable from 10 s to 10 min
- Light level threshold adjustable from 5 to 1275 lux

3-wire, with neutral

- Allow the control of:
 - 0 to 50 W LED and compact fluorescent lamps
 - 0 to 200 VA LED, CFL and halogen lamps with ferromagnetic or electronic ballast
 - 0 to 150 VA fluo tubes with ferromagnetic or electronic ballast
 - 0 to 400 W halogen (230 V) and incandescent lamps
- Only 1 sensor per circuit. No remote manual control with push-button
- Consumption on standby: 0.55 W
- White

General characteristics

Niloé™ - automatic switches and dimmers

- Mechanisms supplied with cover plates and support frames in flow-pack
- To be equipped with plates
- Screw terminals
- Fixing with screws or claws (supplied)

Documentation

Catalogue pages & additional information

- [Description page \(p.532\)](#)

Installation & technical data

- [F02161EN-00](#)

Installation instructions & related documents

- [LE09176AA_1](#)