

CAT. N° 6 624 52



## AUTOTEST/ADRESSABLE LED EMERGENCY LUMINAIRE TWINSPOT - 2 X 750 LM - 1H

Pack (number of units)	1
Volume (dm <sup>3</sup> )	14,07
Weight (g)	3 480,00

### Product characteristics

#### Autotest and addressable LED spotlight luminaire - Non-Maintained (NM)

- 2 x 750 lm – 1h
- Incorporates an automatic self-testing system that checks periodically the emergency lighting function:
  - weekly test of emergency lighting mode
  - quarterly test of battery duration
- Tests result is visible via 2 signalling LEDs (green = OK and yellow = defective) on the luminaire
- Addressable function is activated by setting an ID on each luminaire with infrared configuration tool (Cat.No 0 626 10) and wiring a complementary BUS line
- Operating state of all addressable luminaires can be centralized by the control interface Cat.No 0 626 00 and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building's plan on Legrand Vision System (L.V.S. 2) PC software

### General characteristics

#### LED Twinspot emergency lighting luminaires

- High performance LED non maintained emergency lighting luminaires
- Certified to IEC and EN 60598-2-22 standards
- High power LEDs spotlights with optimized lighting distribution
- Low consumption electronic switching power supply
- High capacity terminals: 2 x 2.5 mm<sup>2</sup> - IP 55 - IK 07
- Duration: 1, 2 and 3 hours. Ni-Cd batteries. Recharge time: 24h
- Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation
- Power supply: 230 V~ ± 10% - 50/60 Hz. Class II
- Rest mode with remote control device Cat.No 0 039 01 to avoid battery discharge in case of voluntary power cut
- Surface mounting installation with 4 wall-mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.679\)](#)
- [Description page \(p.688\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)



#### Agreements & certificates of conformity

- [OC / CB - FR\\_703823](#)
- [ENEC - ENEC\\_1075](#)



#### Installation instructions & related documents

- [LE08514AC](#)