

CAT. N° 8 320 10



DOUBLE POLE SWITCH SYNERGY - 20 A 250 V~ - SLEEK DESIGN BRUSHED STAINLESS STEEL

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,462 |
| Weight (g) | 165,00 |

Product characteristics

Double pole switches 20 A - 250 V~

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 35 mm deep
- Supplied with 1 gang side extension (3 mm thick) in case of extra wiring space needed
- Nominal plate dimensions: 86 x 86 mm

DP switches

- Brushed stainless steel

General characteristics

Synergy™ - double pole switches - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Installation & technical data

- [F02257EN/00](#)



Agreements & certificates of conformity

- [ASTA - 782](#)
- [OC / CB - FR 686293A/A1](#)