

CAT. N° 4 159 30



DX³ STOP ARC 6000 WITH BOTTOM SIDE SUPPLY - 1P+N ON RIGHT-HAND SIDE 230 V~ - 13 A - 2 MODULES - C CURVE

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,369 |
| Weight (g) | 205,00 |

Product characteristics

Arc fault detection circuit breakers

- Breaking capacity:
- 6000 - EN/IEC 60898 - 230/240 V~
- Compatible with prong-type supply busbars

Single pole + neutral 230 V~

- Neutral on right-hand side
- C curve
- Nominal rating I_n : 13 A
- Number of modules : 2

General characteristics

DX³ Stop Arc - bottom side supply - arc fault detection devices from 10 to 20 A

- Conform to IEC/EN 62606
- Can be equipped with DX³ signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

Documentation

Catalogue pages & additional information

- [Description page \(p.063\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F02541EN-02](#)

Installation instructions & related documents

- [LE10543AA](#)

Environmental product profile

- [Environnemental product sheet n°8 E0089A-EN](#)