

CAT. N° 4 159 51



DX³ STOP ARC 6000 WITH TOP SIDE SUPPLY - 1P+N ON LEFT-HAND SIDE - 30 MA - AC TYPE 230 V~ - 16 A - 3 MODULES - C CURVE

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,521 |
| Weight (g) | 293,00 |

Product characteristics

Arc fault detection residual current circuit breakers

- Breaking capacity:
 - 6000 - IEC 61009-1 - 230/240 V~

Single pole + neutral 230 V~ AC Type 30 mA

- Neutral on left-hand side
- C curve
- Nominal rating I_n : 16 A
- Number of modules : 3

General characteristics

DX³ Stop Arc - top side supply - arc fault detection devices from 10 to 20 A

- Conform to IEC/EN 62606 and GB/T31143-2014
- Compatible with prong-type supply busbars
- Can be equipped with DX³ signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

Documentation

Catalogue pages & additional information

- [Description page \(p.063\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F02547EN-01](#)

Installation instructions & related documents

- [LE10542AA](#)