

CAT. N° 0 470 29



## FILTERED RECTIFIED POWER SUPPLY 1 PHASE - PRIM 230-400 V / SEC 24 V= - 1200 W

Pack (number of units)	1
Volume (dm <sup>3</sup> )	169,168
Weight (g)	73 300,00

### Product characteristics

#### Single-phase power supplies

- Consisting of:
  - a safety transformer with interference filtering
  - double operating terminals
  - filter capacitors
  - fused protection in the secondary
  - a green operating voltage present indicator

#### 24 V=

- 230-400 V ± 15 V~ (primary) / 24 V= (secondary)
- Output : 1200 W
- Current : 50 A
- Terminal capacity Flexible cables Input : 16
- Terminal capacity Flexible cables Output : 16

### General characteristics

#### Filtered rectified power supplies

- High reliability power supplies without any pollution on electrical networks
- Supplied with an insulated coupling bar for fast connection between the – and T terminals up to 15 A
- Clip-on only up to 24 W, clip-on or screw fixing up to 120 W
- Above 120 W: screw fixing
- Conform to standards IEC and EN 61558-2-6, UL 60950 and CAN/CSA-C22.2 No 60 950.00
- UL USA and Canada agreements up to 240 W
- Products suitable for building equipment conforming to standards EN 61131-2, EN 60204 and EN 60439-1

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.370\)](#)