

CAT. N° 6 027 98

IP41 KIT FOR XL<sup>3</sup>-N 250 DISTRIBUTION BOARDS

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

## Product characteristics

## Accessories

## IP 41 kit


- For XL<sup>3</sup>-N 250 distribution boards

## General characteristics

XL<sup>3</sup>-N 250 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers; IP 40 (IP 41 with the kit Cat.No 6 027 98) - IK 08 with door
- Conform to standard IEC 61439-2; Type tested; tested and certified by third part laboratory
- Maximum voltage 480 V~; Rated short-time withstand current (I<sub>cs</sub>): 17 kA 0.2 s; Rated peak withstand current (I<sub>pk</sub>): 34 kA
- Ambient temperature: 50 °C continuously
- Zinc coated metal; Grey RAL 7035
- Supplied with: surface or flush-mounting box, reversible door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

## Documentation

 Catalogue pages & additional information

- [Description page \(p.210\)](#)
- [Technical page \(p.211\)](#)