

CAT. N° 6 044 01



XL³-N 125 E DISTRIBUTION BOARD - 18 OUTGOING TERMINALS - MAX. 125 A

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Distribution boards up to 125 A

Maximum rating 125 A

- Flush or surface mounting
- Equipped with 4 rail for main circuit breaker : 3P or 3P + N (Neutral on the right-hand side), 1 module/pole, 4 rail mounting MCB
- Number of poles : 18 outgoing terminals
- No of 3P ways : 6

General characteristics

Convivio™ 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers
- IP 40 - IK 08 with door
- Conform to standard IEC 61439-3: busbar type tested (Lovag certified)
- Maximum voltage 480 V~; Rated short-time withstand current (I_{cw}): 17 kA 0.2 s
- Rated peak withstand current (I_{pk}): 34 kA
- Ambient temperature: 50 °C continuously
- White RAL 9003
- Supplied with: surface or flush-mounting box, door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

Documentation

Catalogue pages & additional information

- [Description page \(p.208\)](#)
- [Technical page \(p.209\)](#)

Installation & technical data

- [F02538EN-01](#)

Installation instructions & related documents

- [LE07122BB](#)