

REF . 1 466 26



## STABILISED SWITCHED MODULES POWER SUPPLY -SINGLE-PHASE -75-960 W-OUTPUT 24 V= -960 W



Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	5,785
Poids (g)	2 560,00

### Caractéristiques du produit

#### Single-phase 75 - 960 W for loads with strong inrush current

- Ability to supply temporary overcurrents (up to 150% for 3 sec)
- High efficiency (up to 94%)
- Low harmonic pollution due to the integrated PFC filter (from 120 W)
- Adjustable output voltage
- Aluminium casing

#### Input voltage: 200 to 240 V~ Output voltage: 24 V=

- Nominal power : 960 W
- Nominal rating : 40 A
- Setting range : 24 to 28 V
- Width : 110 mm

### Caractéristiques générales

#### Stabilised switched mode power supplies - single-phase

- Conforming to standards UL 508, IEC EN 60950-1 and IEC EN 61204-3
- UL-approved in USA and Canada
- Operating frequency: 50/60 Hz
- Output voltage present indicator
- Potentiometer for adjusting the output voltage on front panel
- With signal or relay contact for feedback on the status of the active output voltage (except 75 W)
- Connection with copper conductors only
- For mounting on a symmetrical rail depth 7.5 mm and 15 mm

### Documentation associée

#### Catalogue pages & additional information

- [Description page \(p.368\)](#)
- [Stabilised switched mode power supplies](#)

#### Installation & technical data

- [F02124EN-00](#)

#### Installation instructions & related documents

- [LE07894AA](#)

#### Agreements & certificates of conformity

- [UL listed cULus - E223674](#)