


Product sheet



LEGRAND

Autotest/adressable LED emergency luminaire Twinspot - 2 x 750 lm - 1h

REF. 662452 | EAN. 3414970575814

> [Visit e-catalogue](#)

Product characteristics

- LED Twinspot emergency lighting luminaires - High performance LED non maintained emergency lighting luminaires - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs spotlights with optimized lighting distribution - Low consumption electronic switching power supply - High capacity terminals : 2 x 2.5 mm² - IP 55 - IK 07 - Duration : 1, 2 and 3 hours. Ni - Cd batteries. Recharge time : 24h - Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Rest mode with remote control device Cat.No 0 039 01 to avoid battery discharge in case of voluntary power cut - Surface mounting installation with 4 wall - mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)
- Autotest and addressable LED spotlight luminaire - non-Maintained (NM) - 2 x 750 lm €" 1h - Incorporates an automatic self - testing system that checks periodically the emergency lighting function : - weekly test of emergency lighting mode - quarterly test of battery duration - Tests result is visible via 2 signalling LEDs (green = OK and yellow = defective) on the luminaire - Addressable function is activated by setting an ID on each luminaire with infrared configuration tool (Cat.No 0 626 10) and wiring a complementary BUS line - Operating state of all addressable luminaires can be centralized by the control interface Cat.No 0 626 00 and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building€™s plan on Legrand Vision System (L.V.S. 2) PC software

Documentation

TECHNICAL DOCUMENTATION

→ [LE08514AD.pdf](#) | PDF (1.87Mo)

Agreements & Certificates

 [SDS - Battery NiCd JYH.pdf](#) | PDF (0.33Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0912.pdf](#) | PDF (0.07Mo)