

Product sheet



LEGRAND

Autotest/adressable luminaires U34 LED - 1h duration with opal diffuser - 250 lm

REF. 662160 | EAN. 3245066621609

> [Visit e-catalogue](#)

Product characteristics

- U34LED environment friendly - indoor self - contained emergency lighting luminaires LED - LED Maintained/non-maintained units - High power LEDs with specially designed lenses optimizing the lighting distribution - IP 42 - IK 07 - Class II - Power supply : 230 V $\pm$ 10% - 50/60 Hz - Very low consumption switching power supply - Fully recyclable after removing - Environment friendly Ni - MH batteries - Removable plug - in plate to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5 mm² - Charge monitor with a green LED - Can be equipped with metallic protection grids Cat.Nos 0 626 92/93
- Autotest and addressable luminaires - Maintained/non-maintained (M/NM) - Autotest/addressable luminaires incorporate an automatic self - testing system - Tests result is visible on 2 signalling LEDs (green - OK and yellow - defective) - Addressable function is activated by setting an ID on each luminaire with infrared configuration tool (Cat.No. 0 626 10) and wiring a complementary BUS line - Operating state of all addressable luminaires can be centralized by the control interface (Cat. No. 0 626 00) and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building's plan on Legrand Vision System (LVS2) PC software Cat.No 0 626 021 h duration with transparent diffuser - 250 lm - 1h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

→ [LE05090AB.pdf](#) | PDF (0.63Mo)

Agreements & Certificates

 [OC / CB-690885](#) | (1.17Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0908.pdf](#) | PDF (0.06Mo)

 [Legrand 662160 U34LED 250LM-1H M.zip](#) | ZIP