

Product sheet



NEXPAND LEGRAND

Cabling cabinet 19" with glass front door and blind steel rear door 24U 800x800x1300mm supplied with side panels

REF. 446429 | EAN. 3414972524131

The 19" cabling cabinets has a glass front door and a blind steel door in the back. Delivered with side panels and levelling feet

> [Visit e-catalogue](#)

Description

The 19" cabling cabinets has a glass front door and a blind steel door in the back. Delivered with side panels and levelling feet

Product characteristics

- Capacity 24U, 800mm width and 800mm depth
- Doors are fitted with a Fix-easy swivel handle with a EK333 locking to ensure security. Door can open 165° in case of bayed cabinets or 260° in case of stand-alone cabinets
- Light, solid and demountable aluminium frame with the capacity to handle 1500kg of static load
- Cabinet equipped with 4x19" profiles including height indication. Threaded mounting rails in width, depth and height direction enable stepless adjustability (for example cable management)

Recommendation / Restriction

- The textured polyester coating in the same color as the cabinet provides excellent resistance to corrosion and scratching.
- This server cabinet is intended for digital infrastructures. Delivered with side panels. It has a permissible load up to 1500kg. It can be integrated in installations complying with the following standards: EN-50173-1, EN 50174-1 & 2, C 90-480-1 & 2, ISO IEC 11801, NF C 15-100, IEC 60364-4-41

The product's benefits

Installation

- Roof: 3 cut-outs (the left and right ones have blindplates and brushes, the center one has a blind plate). Mounting rails implemented on the top of the cabinet enable flexible adjustability of accessories. Power distribution can also be placed on top of the cabinet enabling power distribution through cabling and busbars.

Usage

- Cabinet equipped with 4 leveling feet that can be adjusted

Advantages

- Cabinet equipped with 4x19" profiles including height indication
- Optimal accessibility for cabling and optimal positioning for PDU's up to 32A plugs shall fit
- Protected against solid objects larger than 12.5mm (IP20) and mechanical impact with an energy of 5 joules (IK08)

Documentation

TECHNICAL DOCUMENTATION



Technical Sheet | PDF (12.21Mo)