

CAT. N° 6 624 34



EMERGENCY LUMINAIRE B65 - AUTOTEST/ADDRESS MAINT./NON MAINT. - 350 LM - 1H - LED

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 2,387 |
| Weight (g) | 758,00 |

Product characteristics

Autotest and addressable luminaires - Maintained/Non-maintained (M/NM)

- Autotest/addressable luminaires incorporate an automatic self-testing system in order to check emergency lighting
- Tests result is visible on 2 signalling LEDs (green-OK and yellow-defective)
- Addressable function is activated by setting an ID on each luminaire with configuration tool (Cat.No 0 626 10) and wiring a complementary BUS line
- Operating state of all addressable luminaires can be centralized by the control interface (Cat.No 0 626 00) and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building's plan on Legrand Vision System (LVS2) PC software Cat.No 0 626 02
- These Maintained luminaires can also operate in Non-maintained mode according to the wiring of normal lighting
- 350 lm - 1h (LEDs)

General characteristics

B65 LED - weatherproof self-contained emergency lighting luminaire LED

- Weatherproof LED maintained and non-maintained units
- Certified to IEC and EN 60598-2-22 standards
- High power LEDs. IP 65 - IK 07
- Plug-in base to ease fixing, cabling and connection
- Duration: 1 and 3 hours. Ni-Cd or Ni-MH batteries. Recharge time: 24 hours
- Charge monitor with a green LED. Power supply: 230 V ± 10% - 50/60 Hz. Class II
- High-capacity screw terminals (2 x 2.5mm²)
- 3 flexible cable entries for Ø16, 20 and 25 mm tubes
- Can be equipped with metallic protection grids Cat.Nos 0 626 90/92

Documentation

Catalogue pages & additional information

- [Selection chart \(p.679\)](#)
- [Description page \(p.686\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

Installation & technical data

- [S000083090EN-2](#)

Installation instructions & related documents

- [LE06964AD](#)